



FOCAL LENGTH (EFL): 100 ± 1
 BACK FOCAL LENGTH (BFL): 96,01

1 1550nm V-COAT
 R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 51,68 CX Øe 29 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 29 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING			TITLE	30mm Dia x 100mm FL, 1550nm V-Coat Coated, Plano-Convex Lens
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO
			SHEET T SIZE	A4
			SHEET	1 OF 1