



FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $15,94$

1 1064nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 1064\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 8,25 CX \varnothing_e 8,1 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 6/ -	GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL \varnothing_e 8,1 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 2,18' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING			TITLE	9mm Dia x 18mm FL, 1064NM V-COAT Coated, Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	25884	SHEET 1 OF 1